

# MetHumi - Humidity Instrument for Mars MetNet Lander

M. Genzer, J. Polkko, A.-M. Harri, W. Schmidt, J. Leinonen, T. Mäkinen , H. Haukka and S.Merikallio Finnish Meteorological Institute, Helsinki, Finland (maria.genzer@fmi.fi)

#### The MetNet Mission

The MetNet Mission focused on the Martian atmospheric science is based on a new semihard landing vehicle called the MetNet Lander (MNL). The scientific payload of the MetNet Mission encompasses separate instrument packages for the atmospheric entry and descent phase and for the surface operation phase.


### MetHumi Humidity Instrument

Miniature MetNet Humidity Instrument is based on MSL/REMS design and Vaisala Inc. Humicap® sensor and transducer electronics that have been used in Vaisala radiosondes. MetHumi is specially designed to work on the Martian surface.


- •MetHumi is a capacitic type of sensing device where an active polymer film changes capacitance as function of relative humidity.
- •One MetHumi device package consists of one humidity transducer including three Humicap® sensor heads, an accurate temperature sensor head (Thermocap® by Vaisala, Inc.) and constant reference channels.
- •MetHumi is small, lightweight (15 grams) and has low power consumption (15 mW)
- it survives even -135°C ambient temperature. •Humicap® sensor heads are temperature dependent, they require accurate temperature measurement by a tempera-

•MetHumi performs relative humidity measurements in range of 0 – 100%RH down to -70°C ambient temperature and

- ture sensor (MetHumi uses Vaisala Thermocaps®) •MetHumi instrument can be regenerated to remove contamination off the Humicap® chip surface by a heating treat-
- ment using an integrated heating resistor.




Humicap® humidity sensor elements




MSL Humidity device testing

### Heritage and Future

- Earlier version of the device and sensors was used in the Mars-96 landers.
- MSL/REMS Humidity sensor Flight Model was delivered in 2008 (to be launched in 2011).



MSL Humidity sensor calibration



MetNet Mission humidity instrument design

Humicap® test data fitting



## Specifications

- •Accuracy: 8 % RH at -70°C, 6 % RH or better at -50°C to 0°C
- Operational temperature range: +25°C to -70°C
- •Survival temperature: -135°C
- More information from the MetNet Mission website http://metnet.fmi.fi